1. Model FL-CC1614-2M

2. Application For 2/3 Format Camera

3. Specification

3-1. Physical (As per the attached drawing)

(1) Dimensions $\phi 29.5 \text{ mm} \times 33.2 \text{ mm}$

(2) Weight 63 g

(3) Mount C -Mount (1 – 32 UN – 2A)
 (4) Filter Screw Size φ 27 mm . P = 0. 5 mm

3-2. Optical

(1) Focal Length $16 \text{ mm } \pm 5\%$

(2) Max. Aperture Ratio 1: 1.4

(3) Iris Range F / 1.4 to F / 16

(4) Angle of View Diagonal 38.28° Horizontal 30.97°

Horizontal 30.97° Vertical 23.41°

 (5) Picture format
 8.8 mm × 6.6 mm

 (6) Focusing Range
 Inf. to 0.25 m

 (7) Back Focal Length
 14.61 mm (in air)

(8) Flange Back Length $17.526 \text{ mm} \pm 0.05 \text{ mm}$ (in air)

3-3. Mechanical

(1) Focusing Mechanism Straight Helicoid

Rotation Angle 154.3°

Rotation Torque 0.2N·cm to 7.0 N·cm Focus Ring can be fixed at any positions by

3 fixing screws (A) or 1 thumb screw (refer to external view)

(2) Iris Mechanism Non-click, Close-down

Rotation Angle 89.3°

Rotation Torque 0.5N·cm to 7.0 N·cm

Iris Ring can be fixed at any positions by 3 fixing screws (B)

or 1 thumb screw (refer to external view)

3-4 Environmental Temperature Range −20°C to +50°C

4. Accessories

(1) Front Lens Cap1 piece(2) Rear Lens Cap1 piece(3) Fixing Screw A for Focus Ring3 pieces(4) Fixing Screw B for Iris Ring3 pieces

(5) Thumbscrew for Focus Ring 1 pieces (for Optional Usage)
(6) Thumbscrew for Iris Ring 1 pieces (for Optional Usage)

(7) Packing Box 1 piece